



Tapered nose for easy working in confined areas and close tip cutting. Short jaws and beveled cutting edges permit close cutting of wire. Induction-hardened cutting knives for long life. Hot-riveted joint ensures smooth action and no handle wobble. Plastic-dipped handles for comfort and ease of identification. Custom, US-made tool steel.

Specifications

Type:	Diagonal-Cutting Midget Pliers	Overall Length:	4.25" (108 mm)
Material:	Steel	Nose Type:	Tapered
Jaw Length:	0.5" (12.7 mm)	Jaw Width:	0.438" (11.1 mm)
Jaw Thickness:	1/2" (12.7 mm)	Jaw Capacity:	3/4" (19.1 mm)
Cutting Knives:	Semi-flush	Cut Style:	Semi-flush
Joint Type:	Hot-Riveted	Handle Colour:	Light Blue
Handle Finish:	Plastic-dipped	Handle Length:	3.125" (79.4 mm)
Insulated:	No	Tether capable:	No
Weight:	0.12 lb (0.05 kg)		