



60-degree bent nose for maximum work visibility in confined areas. Easily bends and forms fine wire. Polished inside jaws and radiused jaw edges prevent nicking wire. Spring-loaded for self-opening action. Curved handles provide greater tool control.

Specifications

Overall Length: 4.75" (120.7 mm)

Jaw Length: 1" (25.4 mm)

Jaw Width: 0.406" (10.3 mm)

Jaw Thickness: 1/4" (6.4 mm)

Jaw Capacity: 1.28" (32.5 mm)

Point Diameter: 1/16" (1.58 mm)

Handle Colour: Light Blue

Handle Finish: Plastic-dipped

Weight: 0.13 lb (0.06 kg)