



Prokit's Industries CO., LTD.

5F, No.7, Lane 130,  
Ming-Chung Rd., Hsin-Tien Dist,  
New Taipei City, Taiwan, R.O.C. Post code: 23114  
Tel: 886-2-2218-3233; Fax: 886-2-2218-2722

<http://www.prokits.com.tw> Email: [pk-sales@mail.prokits.com.tw](mailto:pk-sales@mail.prokits.com.tw)

## PRODUCT SPECIFICATION

MT-7029

Noise-Filtering NetworkPoE Toner & Probe



\*\*\* Picture for reference only. All specifications are subject to change by supplier. \*\*\*

Specifications:

Transmitter/Toner/Master :

- Tone mode: Two-note tone
- Compatible connectors: RJ45 (8 pin), RJ11 (6 pin)
- Cable type: Twisted pair cables (UTP、STP、Cat. 5e、Cat. 6、Cat. 7), Cat. 3 telephone cables, Coaxial cables (RG6、RG58、RG59、RG62 and others for CATV/CCTV)
- Function selection: 1 Power switch & 4pcs function button
- Cable map and pairs LEDs display: 8 Indicator LED + 1 Grand LED
- Cable test effect and faults indication: Good (Connected、Straight), Open (No connection), Short, Crossed
- Continuity test ( $\Omega$ ):  $\leq 300$
- Shielded indication: Yes
- Loop-back(TX/RX port): Yes
- Buzzer indication: Non

- Phone line polarity indication: Yes
- Validating telephone service: Yes
- Size (mm) length: 138
- Size (mm) width: 80
- Size (mm) height: 35
- Low battery (V): 6.5
- Power source (V): DC 9.0V(NEDA 1604/ 6F22 DC9V ×1pcs, Not included)
- Material character of housing: Single color non-slip
- Material of housing: ABS
- Color of housing: Gray
- Net weight (g) w/o batteries & accessories: 140

#### Receiver/Probe/Remote :

- Signal status indication: 1 LED indicator
- Compatible connectors: RJ45 (8 pin)
- Function selection: Push button & 3 Position switch & Rotary switch
- Cable map indication: 8 Indicator LED + 1 Grand LED
- Shielded indication: Yes
- Buzzer indication: Yes
- earphones jack: Yes
- Size (mm) length: 203
- Size (mm) width: 50
- Size (mm) height: 32
- Net weight (g) w/o batteries & accessories: 95
- Material character of housing: Single color non-slip
- Material of housing: ABS
- Color of housing: Gray
- Power source (V): DC 9.0V(NEDA 1604/ 6F22 DC9V ×1pcs, Not included)

#### Standard accessories :

- Manual : Chinese and English
- Cord sets/Length (cm) : RJ45 (8 pin) to RJ45 (8 pin) patch cords 205mm ×2 pcs, 2pcs of 205mm RJ11 Connector, 450mm RJ11(2)TO
- Alligator clip
- Carrying case : Soft nylon carrying case ×1 pcs
- Carrying case size (mm) L×W×H : 220\*130\*60

#### Individual Packing

- Packing: Color Box

\*\*Remark: Pro'skit Brand\*\*

~ THE END ~