







Rectangular Connectors GDM Series

Technical Information

RMC 480 RMCB 480			
	Description	Order Designation	Order No.
	Crimping flat contact (blade), suitable for GSC series connectors, cable cross-section: 0.5 to 1.5 mm ² (B crimping) RMC 480: Pack size 100 RMCB 480: 3000 items on a reel	RMC 480	731470021
		RMCB 480	731468001
XZC 0702			
	Description	Order Designation	Order No.
	Crimping tool for GDM and G series contacts, color: red Cable cross-section for contact: RMC 280, 0.5 to 1 mm ² , profile I, Order No. 731 991-021 RMC 480, 0.5 to 1.5 mm ² , profile II, Order No. 731 470-021	XZC 0702	932507003
GDM 3-7 NBR pale brown GDM 3-17 VMQ red GDM 3-21 EPDM			
	Description	Order Designation	Order No.
	Flat gasket for GDM series rectangular connectors (type A) NBR: -30 °C to +90 °C VMQ (silicone): -40 °C to +125 °C EPDM (LABS -free): -40 °C to +125 °C Pack size: 50	GDM 3-7 NBR pale brown	730801002
		GDM 3-17 MPQ red	731740002
		GDM 3-21 EPDM brown	731739004
GDM 3-16 NBR black GDM 3-19 VMQ coral red			
	Description	Order Designation	Order No.
	Profile gasket for GDM series rectangular connectors (type A) NBR: -30 °C to +90 °C VMQ (silicone): -40 °C to +125 °C Pack size: 50	GDM 3-16 NBR black	731531002
		GDM 3-19 VMQ coral red	731532002
GSE 2000-2 NBR pale brown GSE 2000-3 EPDM			
	Description	Order Designation	Order No.
	Flat gasket for appliance connector GSE... (type A) NBR: -30 °C to +90 °C EPDM (silicone-free): -40 °C to +125 °C Pack size: 50	GSE 2000-2 NBR pale brown	733973002
		GSE 2000-3 EPDM	733846003
GSAZ 35/43 NBR black GSAZ 40/62 NBR black GSAZ 60/120 NBR black			
	Description	Order Designation	Order No.
	Cylinder profile gasket for appliance male connector GSAZ - 35 to 43 mm diameter - 40 to 62 mm diameter - 60 to 120 mm diameter (type A) NBR: -30 °C to +90 °C Pack size: 50	GSAZ 35/43 NBR black	733262002
		GSAZ 40/62 NBR black	733264002
		GSAZ 60/120 NBR black	733266002