


P1,P2: M-269E
 P3: M-438A
 P4: M-323C

Customer No: No.1



3267-11

P1	P2	P1	P2
1	1 BROWN	14	14 ORANGE
2	2 WHITE	15	15 YELLOW
3	3 SHIELD	16	16 WHITE
4	4 RED	17	17 GREEN
5	5 WHITE	18	18 WHITE
6	6 RED	19	19 SHIELD
7	7 PURPLE	20	20 BLUE
8	8 SHIELD	21	21 WHITE
9	9 ORANGE	22	22 SHIELD
10	10 WHITE	23	23 GREY
11	11 SHIELD	24	24 WHITE
12	12 YELLOW	22	22 SHIELD
13	13 WHITE	SHIELD	SHIELD
14	14 SHIELD		

* NOTE: All relevant materials are complied with RoHS directive .

No.	DESCRIPTION	Q'TY	Supplier
5	UL1061 26AWG INSULATOR WIRE, LENGTH 28mm, DRAWING No.EH002601C-013	2	M304
	BLACK HEAT SHRINK TUBE ϕ 0.8*8mm	16	M743
	BLACK HEAT SHRINK TUBE ϕ 2.6*6mm	14	M743
	BLACK HEAT SHRINK TUBE ϕ 1.5*2mm	14	M743
	DVI25 TINPLATE	2	M935
4	ASSEMBLY PVC BOOT, COLOR BLACK	2	M304
4	UL20276 [(28AWG*1P+AL+D+M)*7c+(28AWG*1PAIR)+(28AWG*3C)]+AL+D+AMA BRAID OD 8.6mm, JACKET BLACK, DRAWING No.EAAB2807P2801P2803C-290	L-20mm	M304
	FERRITE CORE 17.5*9.5*28.5mm	2	M113
3	MOLDED PVC BLACK		M304
2	MOLDED THUMBSCREW #4-40, LENGTH 44.25mm, BLACK	4	M95
1	DVI25 MALE, GOLD PLATED ON CONTACTS & METAL HOOD, BLACK INSULATOR	2	M108

APPROVED		<p>COMTOP CONNECTIVITY SOLUTIONS INC. 15181 Fairfield Ranch Road #100, Chino Hills, CA 91709 Tel.: (909) 597-0883, Fax: (909) 597-0939</p>	Cable Length Unless Other Spec. Tolerances: 0 ~200mm ±10mm 201~1000mm ±20mm 1001 ~1500mm ±25mm 1501~2100mm ±30mm 2100mm↑ ±40mm		
CHECKED	HU				
DRAWING	MEI				
DATE	05/MAY/11	ITEM NO.	10DV-071XX-G	UNIT:mm	