

## TECHNICAL REFERENCE:

Voltage: AC100-240V 50/60HZ

POWER: 120w

Light Source: 36 PCSx3W RGB

Material: Cast-Aluminum body

DMX Channels: 6 CH

Packing Container : 6 PCS/Carton

Inner Package: 235\*235\*350 MM

Out Package: 740\*490\*370 MM

N.W.: 14.4 kg/carton

G.W.: 18.5kg/carton



### VISIT US ONLINE:

*Have a question?*

*Need service or repair?*

*Want to leave a comment?*

[PyleUSA.com/ContactUs](http://PyleUSA.com/ContactUs)

# PYLE

# PYLE

PyleUSA.com

## PDJLT30



## LED STAGE LIGHTING User Manual

## DESCRIPTION

- With the music rhythm, light shines accordingly. Attracting people's eyes.
- Strobe effects, red, green and blue three colors change.
- Its light spot on the wall, the effect likes glass ball, very bright and powerful.
- High quality warranty, safe and reliable.
- Long working life, excellent stability (can reach 60,000.00 hours in general circs).
- Small and exquisite appearance.
- Suitable for disco, ballroom, KTV, bar, stage, club, party etc.

## SECURITY:

1. Make sure that the user voltage is not higher or lower than the regulated value from this user manual.
2. Please take more attention while installing the fixtures. Avoid touching exposed AC cord or will cause deadly accident.
3. When installing the fixtures, make sure the fixtures are not exposed in extremely hot, humid or dusty environment. Make sure the distance between the fixture and the lighted object is not less than 0.5 meter. Make sure there is no combustibile or explosive object around 0.5 meters.
4. Please operate the light fixture after becoming very familiar with the functions. In most cases, the light fixture will be broken by incorrect operation. Don't shake or do anything rudely to the light fixture, or it will cause problems.

## SETTING:

### PDJLT30 Control:

Channel	Channel data	Function instruction
CH1	0-255	Master dimming
CH2	0-255	Red dimming
CH3	0-255	Green dimming
CH4	0-255	Blue dimming
CH5	1-255	Strobe control
CH6	1-255	Master function

