



20V MAX* ½ IN. CORDLESS DRILL/DRIVER KIT

PCC601LA



This 20V MAX* ½ in. Lithium Ion Drill/Driver Kit lets you power through the toughest metal drilling, wood drilling, and fastening jobs. With a compact and lightweight design, this Drill/Driver is designed to eliminate user fatigue, but it doesn't compromise on speed and power thanks to its two-speed gearbox and high-output motor. Packed with two PCC680L batteries and a PCC690L charger, this is the kit you need whether you're installing cabinetry, framing out rooms, or fastening hinges on doors

FEATURES & SPECS

FEATURES

- High performance motor delivers 330 Unit Watts Out
- Metal ratcheting chuck minimizes bits slipping in chuck
- LED light brightens dark work areas
- 20V Max Lithium Ion batteries with 1.5 amp/hour cells delivers more power and runtime in a smaller package
- 2 Speed gear box (0-400/0-1,600) delivers the power needed to complete large and small applications
- Battery gauge displays charge remaining in the battery
- Compact size (7 3/4" length) and light weight (3.5lbs) allows tool to work in tight areas and minimizes user fatigue

SPECIFICATIONS

BATTERY TYPE	LITHIUM ION	CHUCK SIZE	1/2"
CHUCK TYPE	KEYLESS	CLUTCH SETTINGS	23
KIT BOX	NONE	MAX POWER	330 UW/O
NO LOAD SPEED	0-1600 RPM	# OF SPEED SETTINGS	2
POWER TOOL TYPE	CORDLESS	TOOL LENGTH	7.75 IN
UNITS WATTS OUT	330		