



TRIAx

connecting the future



LTE WFAV 410 - 1 Input - Wideband Masthead Amplifier & Power Supply Kit

Article number: 370561

Product description:

Wolsey LTE Masthead Amplifier Kit

- F-Connector Masthead Amplifier and Power Supply Kit
- 1 Input 1 Output
- 0-10 dB Variable Gain
- Weatherproof housing
- Fully screened enclosure

Specifications

ORDER INFORMATION	
EAN Number	5702663705616
CHARACTERISTICS	
Type	Amplifier - mast
Max. Output level @ -60 dB IMD	85 dBμV
FREQUENCY	
Input 1 - frequency	470...790 MHz
Input 1 - band	UHF (T)

Input 1 - channels	21...60
LTE protection	@ 800Mhz
GAIN	
Input 1 - gain	0-10 dB
Input 1 - noise figure	<2.2 dB
RETURN LOSS	
Return Loss	10 Typ dB
ELECTRICAL	
Impedance	75 Ω
OPERATIONAL	
DC Operating voltage	12 VDC
DC Current consumption	100 mA
CONNECTORS	
Number of inputs	1
Number of outputs	4
Connector Type	F-female
MECHANICAL	
Product Height	215 mm
Product Depth	60 mm
Product Width	120 mm
Colour	Black
Net Weight	0,540 kg
Tara Weight	0,080 kg
Total Weight	0,620 kg
Remarks	Kit includes WPS 100 Power Supply, 12VDC, 100mA Max Fully screened