



# TRIAx

connecting the future



## LTE WFAV 622 - 1 Input - Wideband Masthead Amplifier & Power Supply Kit

Article number: 370563

### Product description:

#### Wolsey LTE Masthead Amplifier Kit

- F-Connector Masthead Amplifier and Power Supply Kit
- 1 Input 6 Output
- 12-22 dB Variable Gain
- Weatherproof housing
- Fully screened enclosure

### Specifications

ORDER INFORMATION	
EAN Number	5702663705630
CHARACTERISTICS	
Type	Amplifier - mast
Max. Output level @ -60 dB IMD	83 dB $\mu$ V
FREQUENCY	
Input 1 - frequency	470...790 MHz
Input 1 - band	UHF (T)

Input 1 - channels	21...60
LTE protection	@ 800Mhz
<b>GAIN</b>	
Input 1 - gain	12-22 dB
Input 1 - noise figure	<2.2 dB
<b>RETURN LOSS</b>	
Return Loss	10 Typ dB
<b>ELECTRICAL</b>	
Impedance	75 $\Omega$
<b>OPERATIONAL</b>	
DC Operating voltage	12 VDC
DC Current consumption	100 mA
<b>CONNECTORS</b>	
Number of inputs	1
Number of outputs	6
Connector Type	F-female
<b>MECHANICAL</b>	
Product Height	185 mm
Product Depth	60 mm
Product Width	160 mm
Colour	Black
Net Weight	0,610 kg
Tara Weight	0,070 kg
Total Weight	0,680 kg
Remarks	Kit includes WPS 100 Power Supply, 12VDC, 100mA Max Fully screened