


THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MASTER.




* UNLESS OTHERWISE SPECIFIED TOLERANCES
ON DECIMAL IS: ANGLE $\pm 1^\circ$
.XX ± 0.35
UNIT: MM

Electrical:
Contact current rating: 1.5AMPS
Dielectric withstanding voltage: 500VAC
Insulation resistance: 1000 MegOhms Min.
Contact resistance: 30 MilliOhms Max
Operating temperature: -55 °C to +85°C

Materials:

Contacts: Phosphor bronze
Insulator: Thermoplastic UL 94V-0
Shell: Stainless steel
Gold plating: 6 microinch



Front Panel Jack Only Clearance
W/O Latch Feature

Single Panel - Latch Clearance
Panel Thickness 0.062 inch

THESE DRAWINGS AND SPECIFICATIONS ARE THE
PROPERTY OF MH CONNECTORS LTD. AND SHALL NOT
BE REPRODUCED, COPIED OR USED AS THE BASIS FOR
THE MANUFACTURE OR SALE OF APPARATUS WITHOUT
WRITTEN PERMISSION.

DRAWN DATE

JDHNNY

08-21-12

APPROVED

DATE

SCALE

1:1

SHEET OF REV:

1 OF 1 A

MH CONNECTORS LTD.

DRAWING No

MH3101S-8821



THIS SERIES FULLY CONFORMS TO THE
EUROPEAN UNION DIRECTIVES 2002/95/EC
AND 2002/96/EC FOR ROHS COMPLIANCY.

