## ROLINE HQ VGA Cable + Ferrite + DDC, HD15, M/M, 20.0 m

**Product No.** 11.04.5670

ROLINE

**Manufacturer No.** 11.04.5670

**EAN (single piece)** 7611990192267



Manufacturer





- High quality cable for connection of a monitor to a graphics card or VGA splitter or amplifier
- Additionally with two ferrite cores and DDC functionality
- 3 coax lines for the RGB signals and 9 AWG28 wires (all pins connected, incl. pin 9 and pin 15)
- Double screened cable (braided and foil shielding)
- Thumbscrews

Technical specifications	
Manufacturer	ROLINE
Product group	Cable
Product type	VGA Cables
Colour	black
Length	20 m
side 1 connector	D-Sub HD15 M
side 2 connector	D-Sub HD15 M
Side 1 Connector Type	HD D-Sub 15-pin (HD-15), VGA
Side 1 Connector Gender	Male

Side 2 Connector Type	HD D-Sub 15-pin (HD-15), VGA
Side 2 Connector Gender	Male
Area of application	External
Cable shielding	Double screened
Hand locking screws	Yes
Technical particularity	With two ferrite cores and DDC functionality