

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

GP

00

C

REVISE PER ECO-05-006320

01AUG05

TW

JH

Tooling Drawing NO.

USB A: TR00662

USB B: TR00664

Pos.4

Pos.1

1

4

6

5

3

6

4

2

Pos.2

Pos.3

Pos.1

Pos.4

25±5

L+0-50

(25)

TYCO P/N

T/D YYWW

MADE IN CHINA

(13)

(35)

LABEL

NOTES:

1. TESTED FOR CONTINUITY, SHORTS AND OPENS, HI-POT 630V FOR 10MS.

2. CABLE ASSEMBLY MEETS USB 2.0 STANDARDS.

3. EXPOSED CABLE BRAID IS NOT PERMISSIBLE BEYOND OVERMOLD.

4. THE FINAL CABLE ASSEMBLY MAXIMUM LENGTH NOT TO EXCEED 1700MM PER USB SPECIFICATIONS.

5. MEETS REQUIREMENTS OF EU DIRECTIVE 2002/95/EC

PIN ASSIGNMENT :

USB A

2

3

1

4

Shell

Pair 1

White(D-)

Green(D+)

Red(V BUS)

Black(Gnd)

Drain

Braid

USB B

2

3

1

4

Shell

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

0 PLC

± -

1 PLC

± -

2 PLC

± -

3 PLC

± -

4 PLC

± -

ANGLES

± -

MATERIAL

-

FINISH

-

DWN

BOVEY LIU

25FEB02

CHK

J.HUNT

25FEB02

APVD

J.HUNT

25FEB02

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

NAME

USB A TYPE TO USB B TYPE CABLE ASSEMBLY

SIZE

A3

CAGE CODE

00779

DRAWING NO

C-1487587

RESTRICTED TO

-

SCALE

N.T.S

SHEET

1

OF

1

REV

C

tyco

Electronics

Tyco Electronics Corporation

Harrisburg, Pa 17105-3608

AMP 1470-19 REV 31MAR2000