




NOTES:

1. MATERIAL:

HOUSING: PBT+30%GF UL94V0 BLACK COLOR

CONTACT: PHOSPHOR BRONZE 0.20MM THK

TIN PLATED OVER NICKEL

2. CURRENT RATING : 2A (AC/DC)

3. VOLTAGE RATING : 500V (AC/DC)


4. CONTACT RESISTANCE: 30 MILLIOHMS

5. INSULATION RESISTANCE: 500 MEGAOHMS

6. TEMPERATURE RANGE: -55°C TO $+85^{\circ}\text{C}$

7. HUMIDITY: 40°C AND 90-95% RH FOR 96 HOURS

8. RoHS COMPLIANT

3						
2						
1			NAME	COIN CELL HOLDER		
NO.	MODIFICATION	DATE	SCALE	2:1	APPD	
	General Tolerance		UNIT	MM	CHKD	
	Dim: 0.0	± 0.30	MAT' L	AS NOTES	DWN	
	0.00	± 0.20	DATE	MAR. 25. 2008	DR NO	CH23-0308
	Angle: $\pm 3^{\circ}$	0.000 ± 0.10				