

TTK20GY-SD

Grey TeeTube In-line 3 Pole Screw - end barrier contact 5mm to 13mm, 4 mm max conductor size IP68 32A 450V 2 cable entries



SPECIFICATION

Cable Entries	2
Number of Poles	3
Terminal Type	Screw - end barrier contact
Body Material	PA66 / TPE
Colour	Grey
IP Rating	68
Max Conductor Size (Sq mm)	4
Max Current (A)	32
Max Voltage (V)	450
Minimum Temp Rating °C	-40
Maximum Temp Rating °C	125
Minimum Cable Diameter (mm)	5
Maximum Cable Diameter (mm)	13
Comments	Colour to grey
Fixing System	cable
Temperature "T" Rating	T85

DISTRIBUTORS

