

NOTES:

1. MATERIAL


- 1.1 HDMI CABLE: (7/0.10TC\*1P+7/0.10TC+FAM)\*4PCS+7/0.10TC\*3C+7/0.10TC\*1P+AL+7/0.12BC+128/0.12ALM+BLACK PVC JACKET.  
OD:  $\varnothing 6.0 \pm 0.2$  mm  
CABLE MARKING: E324703 AWM STYLE 20276 80°C 30V DVI CABLE .
- 1.2 HDMI 19PIN TYPE A MALE: BLACK INSULATION, GOLD PLATED CONTACTS, GOLD PLATED SHELL .
- 1.3 DVI(24+1) MALE: BLACK INSULATION, GOLD PLATED CONTACTS G/F, GOLD PLATED SHELL G/F.
- 1.4 THUMB SCREW TO BE MOLDED BLACK PVC.
- 1.5 ALL HOOD: MOLDED BLACK PVC.

2. ELECTRICAL

- 2.1 100% OPEN AND SHORT TEST.
- 2.2 CONDUCTOR RESISTANCE: 5 OHMS MAX.
- 2.3 INSULATION RESISTANCE: 10 MEGOHMS MIN.
- 2.4 HI-POT: DC300V/0.01S.

- 3. PACKAGING: A PC/PE-BAG PACKAGING .
- 4. ALL MATERIALS ARE RoHS COMPLIANT.

PIN OUT



P/N

ITEM NO.	L (mm)
CS24785	500 ± 30mm
CS20592	1000 ± 30mm

LENGTH TOLERANCE: X. ± 0.5 .X ± 0.2 .XX ± 0.1	SCALE: FREE	CUS. NAME: CPC		PRODUCT NO:		CUSTOMER NO:		ENG:
	ANGLE TOLERANCE: X° ± 3' .X° ± 1'	UNIT: mm			DRAWING NO: HF2724		PRODUCT DESCRIPTION: HDMI AM/DVI(24+1) M	
VERSION: 00	PAGE: 1/1					CHECKED:		APPROVED:

00	NEW ISSUE	2019-02-12
REV.	MODIFY DESCRIPTION	DATE