

# Han-Eco 10B-HSM1-with SL-M20-glanded



| Part number        | 19 43 110 0250                           |
|--------------------|--|
| Specification      | Han-Eco 10B-HSM1-with SL-M20-<br>glanded |
| HARTING eCatalogue | https://b2b.harting.com/19431100250      |
|                    |  |

#### Identification

| Category                            | Hoods/Housings              |
|-------------------------------------|-----------------------------|
| Series of hoods/housings Han-Eco® B |                             |
| Type of hood/housing                | Surface mounted housing     |
| Description of hood/<br>housing     | With integrated cable gland |

#### Version

| Locking type | Single locking lever |
|--------------|----------------------|
| Size         | 10 B                 |
| Version      | Side entry           |
| Cable entry  | 1x M20               |

#### Technical characteristics

| Limiting temperature                   | -40 +125 °C |
|--|-------------|
| Number of relockings                   | ≥500        |
| Degree of protection acc. to IEC 60529 | IP66        |
| Clamping range                         | 6 13 mm     |

## Material properties

| Material (hood/housing)                   | Polyamide<br>Fibre-glass reinforced |
|---|-------------------------------------|
| Colour (hood/housing)                     | RAL 9005 (jet black)                |
| Material (seal)                           | NBR                                 |
| Colour (seal)                             | RAL 9005 (jet black)                |
| Material (locking)                        | Polyamide<br>Fibre-glass reinforced |
| Colour (locking)                          | RAL 9005 (jet black)                |
| Material flammability class acc. to UL 94 | V-0                                 |



## Material properties

Material flammability class acc. to UL 94 (locking levers)

V-0

## Specifications and approvals

#### Commercial data

| Packaging size                 | 1        |
|--------------------------------|----------|
| Country of origin              | Germany  |
| European customs tariff number | 85389099 |