

# Han-Eco 10B-HTE-for DL-M25-glanded



Part number	19 43 110 0426
Specification	Han-Eco 10B-HTE-for DL-M25-glanded
HARTING eCatalogue	https://b2b.harting.com/19431100426

### Identification

Category	Hoods/Housings
Series of hoods/housings Han-Eco <sup>®</sup> B	
Type of hood/housing	Hoods
Description of hood/ housing	With integrated cable gland

#### Version

Locking type	Double locking lever
Size	10 B
Version	Top entry
Cable entry	1x M25

#### Technical characteristics

Limiting temperature	-40 +125 °C
Number of relockings	≥500
Degree of protection acc. to IEC 60529	IP66
Clamping range	9 17 mm

## Material properties

Material (hood/housing)	Polyamide Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0

## Specifications and approvals

Product data sheet 19 43 110 0426 Han-Eco 10B-HTE-for DL-M25-glanded



### Commercial data

Packaging size	1
Net weight	123 g
Country of origin	Germany
European customs tariff number	85389099