

Han-Eco 16B-HSE-for DL-M32-glanded



| Part number | 19 43 116 0527 |
|--------------------|-------------------------------------|
| Specification | Han-Eco 16B-HSE-for DL-M32-glanded |
| HARTING eCatalogue | https://b2b.harting.com/19431160527 |

Identification

| Category | Hoods/Housings |
|---|-----------------------------|
| Series of hoods/housings Han-Eco [®] B | |
| Type of hood/housing | Hoods |
| Description of hood/ housing | With integrated cable gland |

Version

| Locking type | Double locking lever |
|--------------|----------------------|
| Size | 16 B |
| Version | Side entry |
| Cable entry | 1x M32 |

Technical characteristics

| Limiting temperature | -40 +125 °C |
|--|-------------|
| Number of relockings | ≥500 |
| Degree of protection acc. to IEC 60529 | IP66 |
| Clamping range | 13 21 mm |

Material properties

| Material (hood/housing) | Polyamide Fibre-glass reinforced |
|---|-------------------------------------|
| Colour (hood/housing) | RAL 9005 (jet black) |
| Material flammability class acc. to UL 94 | V-0 |

Specifications and approvals

| Specifications | IEC 61984 |
|----------------|-------------------------------|
| | EN 45545-2 R22: HL1, HL2, HL3 |
| | EN 45545-2 R23: HL1, HL2, HL3 |
| | EN 45545-2 R24: HL1, HL2, HL3 |
| | |

Product data sheet 19 43 116 0527 Han-Eco 16B-HSE-for DL-M32-glanded



Commercial data

| Packaging size | 1 |
|--------------------------------|----------|
| Net weight | 180 g |
| Country of origin | Germany |
| European customs tariff number | 85389099 |