

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

| REVISIONS | | | | DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398 | | | | | |
|-----------|-----|-------------|-------|--|--------|---------|--------|---------|--|
| DCP # | REV | DESCRIPTION | DRAWN | DATE | CHECKD | DATE | APPRVD | DATE | |
| 1491 | Α | RELEASED | JWM | 9/15/03 | НО | 9/15/03 | DJC | 9/15/03 | |
| | | | | | | | | | |



1 ~ 13 pH (typical 0~14pH) Epoxy Body, BNC Connector Body Size: 12mm Dia x 160mm For use with pH Meter 72-6783

DISCLAIMER:

ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

PURPOSES ONLY.

TOI ERANCES.

| DRAWN BY: | DATE: |
|---------------|---------|
| Jeff McVicker | 9/15/03 |
| CHECKED BY: | DATE: |
| Hisham Odish | 9/15/03 |
| APPROVED BY: | DATE: |
| Daniel Carey | 9/15/03 |

| 3 | DRAW | ING TITLE: | | pH Probe | | | | | |
|---|-------|------------|--|---------------------|------|-------------|-----|-----|--|
| | SIZE | DWG. NO. | | | ELEC | TRONIC FIL | .E | REV | |
| 3 | Α | 72-6784 | | | 17 | 17C6509.dwg | | | |
| 3 | SCALI | E: NTS | | U.O.M.: Millimeters | | SHEET: | 1 0 | F 1 | |