

Barrel Vacuum

by **Atrix**™



High Capacity



ATI55H-3

PRODUCT HIGHLIGHTS

WARRANTY

1 Year Limited

3 MOTOR CONFIGURED VACUUM HEAD

Converts your 55 gallon barrel/drum into a large capacity vacuum

POWERFUL

TRIPLE 550 Watt Motors allows the user to control the amount of suction needed per a wide variety of applications by switching on 1, 2 or all 3 motors

SAFE

Can be used in general cleaning with its efficient two stage HEPA filter configuration

APPLICATIONS

Manufacturing, Construction or other situations where large amounts of non-hazardous dry particulate needs to be collected



Ultrafine Vacuums Built to Last. Quality Assured.

www.atrix.com | sales@atrix.com | 1-800-222-6154 | Burnsville, MN, USA

Barrel Vac

by **Atrix**™

SPECIFICATIONS

ATI55H-3

DIMENSIONS

Length: 26" (660 mm)

Width: 26" (660 mm)

Height: 26" (660 mm)

WEIGHT 26 lbs. (11.8 kg)

HOSE DIAMETER

Inside - 2.00" (50.8 mm)

Outside - 2.33" (59.18 mm)

POWER

120v, 550W x 3

CFM

89, 178 or 267

INCLUDED CONTENTS

Barrel Vac by Atrix

A - 28' Power Cord

B - ATIBV55-MH - Triple Motor Head

C - ATIBV55-DA - Barrel/Drum Adapter

D - ATIBCVH1 - Premotor HEPA Filter Cartridge, Main

E - ATIBCVSF - Polyester Pretreated Filter for Main HEPA Filter

F - ATIBV55-12 - 12' Hose w/Ends

G - ATIBV55-WS - 3 Piece Chrome Wand Set

H - ATIBV55-FT - Floor Tool

FILTRATION

2 Stage

HEPA Premotor Filter

Polyester Pretreated Filter

GENERAL INFORMATION

PACKAGING

Dimensions:	L	W	H
Inches:	34	26	38
mm:	864	660	965
Weight:	94 lbs.		
	42.6 kg		

HS Code

8508.11.0000

UPC

8 38067 00343 2

OPTIONAL ACCESSORIES

25' Hose w/Ends
ATIBV55-25



Barrel/Drum Roller Base
ATIBV55-RB



55 Gallon Barrel/Drum
ATIBV55-DRUM

