


KEMET, SSHB10H, AC Line Filters, Dual Mode, 0.032 H

**Dimensions**

L	22mm MAX
T	17mm MAX
H	15.5mm MAX
LL	3.5mm +/-0.5mm
S	10mm +/-0.5mm

Packaging Specifications

Packaging:	Tray
Packaging Quantity:	300
Weight:	10 g

General Information

Series:	SSHB10H
Style:	Through-Hole
RoHS:	Yes
Notes:	Marking: 04 Lot No.
Miscellaneous:	Temperature Rise Maximum: 60 K

Specifications

Voltage AC:	250 VAC
Inductance:	32 mH (10 kHz)
Current:	400 mA
Temperature Range:	-25/+130C
DC Resistance:	2.7 Ohms