

Electrician's Insulated Tools



1000 V Rated

For Safety on the Job



MADE IN USA



**KLEIN
TOOLS®**



For Professionals... Since 1857® USA

Unique Three-Part Insulation with white underlayer provides a warning sign that insulation may be compromised.



Custom US-made tool steel.

Meets or exceeds IEC 60900 and ASTM F1505 tool standards.

Multi-color, sleek design with small thumb guards for ease of handling and storage.

12098-EINS



Selection Guide

Cat No.	UPC Code	Description	Overall Length	Weight
12098-EINS	70191-7	Combination Pliers	8-3/4" (222 mm)	0.86 lbs (0.39 kg)
High-Leverage Diagonal-Cutting Pliers				
2000-28-EINS	72007-9	Tapered Head	8-1/4" (210 mm)	0.74 lbs (0.34 kg)
2000-48-EINS	72008-6	Angled Head	8-1/4" (210 mm)	0.74 lbs (0.34 kg)
High-Leverage Side-Cutting Pliers				
213-8NE-EINS	70192-4	New England Nose	8-7/8" (225 mm)	1.00 lbs (0.45 kg)
213-9NE-EINS	70193-1	New England Nose	9-1/2" (241 mm)	1.19 lbs (0.54 kg)
20009NE-EINS	70194-8	2000 Series, Heavy-Duty Cutting	9-1/2" (241 mm)	1.19 lbs (0.54 kg)
Long Nose & Tongue & Groove Pliers				
203-6-EINS	71048-3	6" Long Nose	6-7/8" (175 mm)	0.30 lbs (0.14 kg)
203-7-EINS	71049-0	7" Long Nose	7-1/2" (191 mm)	0.35 lbs (0.16 kg)
203-8-EINS	71047-6	8" Long Nose	8-5/8" (219 mm)	0.69 lbs (0.31 kg)
502-10-EINS	73001-6	Tongue & Groove	10-1/4" (260 mm)	1.06 lbs (0.48 kg)
Cutters & Strippers				
63050-EINS	63013-2	Cable Cutter	9-5/8" (245 mm)	1.01 lbs (0.46 kg)
11054-EINS	74010-7	8-16 AWG Solid & 10-18 AWG Stranded Stripper	7-5/8" (194 mm)	0.47 lbs (0.21 kg)

Diagonal-Cutting	Side-Cutting	Wire Stripper	Cable Cutter	Long-Nose Pliers
2000-28-EINS	213-9NE-EINS	11054-EINS	63050-EINS	203-7-EINS





Use this Non-Contact Voltage Tester to detect standard voltage in cables, cords, circuit breakers, lighting fixtures, switches, electrical sockets and wires. A bright-green LED will tell you that the tester is working, and also functions as a work light. It changes to red, and warning tones sound, when voltage is detected.

Specifications

Special Features: Green LED turns off and red LED illuminates continuously.

Drop Protection: 9.8 ft (3 m)

Voltage: 50 - 1000V AC

Frequency: 50-500 Hz

Pollution Degree: 2

Standard: CAT IV 1000V

Weight w/batteries: 1.6 oz (45 g)

Batteries: 2 x AAA

Overall Length: 5.5" (139.7 mm)

Overall Height: 1" (25.4 mm)

Overall Width: 0.719" (18.3 mm)

Weight: 0.80 oz (22.7 g)