

Main Specifications

Screen size	31.5
Resolution (max.)	3840x2160

All Specifications

Display

Screen size	31.5
Panel Type	VA Type
Backlight Technology	LED backlight
Resolution (max.)	3840x2160
Brightness	300
Native Contrast (typ.)	3000:1
Viewing Angle (L/R;U/D) (CR>=10)	178/178
Response Time	4
Refresh Rate	60Hz
Aspect Ratio	16:9
Display Colours	1.07 billion colors
Colour Gamut	95% DCI-P3
Display Area (mm)	698.4*392.85
PPI	140
DCR (Dynamic Contrast Ratio) (typ.)	20M:1
Colour Bit	10 bit

Audio

Built-in Speaker	2Wx2
Headphone Jack	Yes

Monitor

Product Colour	Metallic grey
Colour Temperature	Reddish / Normal/ Bluish /user mode
K Locker	Yes
OSD Language	18 Languages (English / Francais / Deutsch / Italiano / Espanol / Polish / Czech / Hungarian / Romanian / Netherlands / Russian / Swedish / Portuguese / Japanese / Chinese / S-Chinese / Arabic/Korean)
HDCP	Yes
VESA Wall Mount	Yes
AMA	Yes

Eye Care

Flicker-free Technology	Yes
Low Blue Light	Yes
Brightness Intelligence Plus (B.I.+)	Yes

Video Enjoyment

Smart focus	Yes
Super Resolution	Yes

Gaming

FreeSync	Yes
----------	-----

Connectivity

HDMI	Yes
DisplayPort	DisplayPort (v1.4)x1
USB Type-C	Yes

Power

Voltage Rating	90~264 AC
Power Supply	Built-in
Power Consumption (on mode.)	76W

Dimension and Weight

Dimensions (HxWxD mm)	522.2X726.4X215
Net Weight (kg)	7.5
Gross Weight (kg)	10.2
Tilt (down/up)	-5° - 15°

Certification

Mac-Compatible	Yes
Windows®-Compatible	Yes
TUV Certificate	Yes