

LED TABLE LAMP



Product Specification

- LED CHIPS: 18 pcs SMD 2835
- CCT: 6500K
- Dimmable mode: Hold Power button for 3
- Power: 6W
- Bluetooth Range: upto 10 meters
- Speaker Output Power: 4.5W
- Charging Voltage: DC 5V (Charging Cable included)
- Hands free Call Function with built in Microphone
- Music Modes: Bluetooth 4.0, AUX (cable included), TF Card slot, USB Slot..

