

## Crimping pliers - CRIMPFOX-P CC 0.75 L - 1064998

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Crimping pliers, for COMBICON crimp connectors with cross section: 0.14 ... 0.75 mm<sup>2</sup>. Unlockable pressure lock, precise parallel crimping, front entry, B crimp, incl. 2 positioning aids

### Your advantages

- Precision-manufactured dies ensure consistently high levels of quality during contact processing
- High crimping force with low manual force
- Marked die stations for precise processing of corresponding cross sections
- Parallel motion sequences of the dies for symmetrical and optimum crimping results
- 
- 
- 

### Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 722979
GTIN	4055626722979
Weight per Piece (excluding packing)	540.000 g
Custom tariff number	82032000
Country of origin	Sweden

### Technical data

#### Dimensions

Length (b)	233 mm
------------	--------

#### General

Compression	B crimp
Designation	Crimping position 1
Max. cross section	0.34 mm <sup>2</sup>
AWG max	22

# Crimping pliers - CRIMPFOX-P CC 0.75 L - 1064998

## Technical data

### General

Designation	Crimping position 2
Max. cross section	0.5 mm <sup>2</sup>
AWG max	20
Designation	Crimping position 3
Max. cross section	0.75 mm <sup>2</sup>
AWG max	18
Die station	Crimping position 4
Min. cross section	0.14 mm <sup>2</sup>
Max. cross section	0.25 mm <sup>2</sup>
AWG min	26
AWG max	24
Weight	450 g
Min. cross section	0.14 mm <sup>2</sup>
Max. cross section	0.75 mm <sup>2</sup>

## Classifications

### eCl@ss

eCl@ss 10.0.1	21043811
eCl@ss 6.0	21043800
eCl@ss 7.0	21043811
eCl@ss 9.0	21043811

### ETIM

ETIM 6.0	EC000168
----------	----------

## Approvals

### Approvals

---

Approvals

EAC

---


Ex Approvals

---

### Approval details

# Crimping pliers - CRIMPFOX-P CC 0.75 L - 1064998

## Approvals

EAC		RU x- DE.xx08.B.02974
-----	---	--------------------------

## Accessories

### Accessories

#### Crimp contact

Accessories - PTCM-MP-P 0,14-0,5 - 1013781



Crimp contact, type of contact: Female connector, connection method: Crimp connection, contact surface: Tin, type of packaging: packed in cardboard

Accessories - PTCM-MP-P 0,34-0,75 - 1013780



Crimp contact, type of contact: Female connector, connection method: Crimp connection, contact surface: Tin, type of packaging: packed in cardboard

Accessories - PTCM-MP-PI 0,14-0,5 - 1013990



Crimp contact, type of contact: Male connector, connection method: Crimp connection, contact surface: Tin

Accessories - PTCM-MP-PI 0,34-0,75 - 1013989



Crimp contact, type of contact: Male connector, connection method: Crimp connection, contact surface: Tin

## Crimping pliers - CRIMPFOX-P CC 0.75 L - 1064998

### Accessories

Accessories - MCC 0,5-MP AU 0,14-0,5 - 1013425



Crimp contact, type of contact: Female connector, connection method: Crimp connection, contact surface: Gold, Conductor cross section flexible: 0.14 ...0.5 mm<sup>2</sup>, type of packaging: packed in cardboard

---

Accessories - MCC 0,5-MP AU 0,34-0,75 - 1013419



Crimp contact, type of contact: Female connector, connection method: Crimp connection, contact surface: Gold, Conductor cross section flexible: 0.34 ...0.75 mm<sup>2</sup>, type of packaging: packed in cardboard

---