







87 **KNIPEX Cobra® VDE Hightech Water Pump Pliers,**
26 **insulated**

DIN ISO 8976
 IEC 60900 DIN EN 60900



- Adjustment by shifting the jaw directly on to the workpiece: fast, secure and comfortable handling
- Opening at the touch of a button apart from the workpiece
- Fine adjustment for optimum adaptation to different workpiece sizes and comfortable gripping position
- Good access to the workpiece due to slim size in the head and joint area
- Self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- Gripping surfaces with special hardened teeth, teeth hardness approx. 61 HRC: low wear and reliable gripping
- Box-joint design: high stability because of double guide
- Pinch guard prevents operators' fingers being pinched
- Chrome vanadium electric steel, forged, multi stage oil-hardened

The adjustment action to adapt to the workpiece is easy and reliable with the KNIPEX Cobra® VDE: place the upper gripping jaw of the opened pliers on the workpiece, push pliers to close, done!

Product Number	UPC 8432210-		Pliers	Head	Handles	 Ø Inch	 Ø Inch / Ø mm	 Inch / mm	adjustment positions	 Inch / mm	 lbs
87 28 250 US			grey atramentized	polished	insulated with multi-component grips, VDE-tested	2	1 31/32 50	1 13/16 46	24	10 250	0,750

technical change and errors excepted



Quick adjustment to the workpiece without using a pushbutton



just push the pliers handle to adjust