

Specifications:

Impedance (Ω)	8 ± 15% at 1000 Hz at 1.0 V
Rated Power (W)	0.5
Max Power (W)	1.0
Resonance Freq Fo (Hz)	600 ± 20% at 1.0 V
Frequency Range (Hz)	Fo ~ 6000
Output S.P.L. (dB)	96 ± 3 at .5w/1m 1.0k, 1.2k, 1.5k, 2.0kHz 79 ± 3 at 1w/1m 1.0k, 1.2k, 1.5k, 2.0kHz
Frame Material	Metal
Operating Temp	-20 to 55°C
Weight (g)	4.5
Options	For other options contact factory

Dimensions: ±0.3 (units: mm)

ROHS Compliant

