

## **Description**

The CiT WK-838 is an excellent ultra-thin low profile, small framed premium keyboard, fitted with a touch membrane under each key you get a smooth and timely response from each press. The WK-838 is compact in size, making it ideal for business or home users with limited desk space and is a great on the go solution.

With a small footprint of 83 keys the WK-838 has all the features you would want from a full size keyboard, with 9 multimedia functions you have access to a range of media applications. By pressing FN + the cursor keys enable you to have four extra commands (Page Up, Page Down, Home and End). The numeric keypad is integrated into the standard keys and with a net weight of only 0.41KGs the WK-838 is the ideal small form keyboard.

## **Key Features**

- **Design** - The WK-838 is an ultra-thin keyboard made using high-quality touch membrane creating robust long-lasting keys during use.
- **Size** - The size of the keyboard is 348 x 145 x 22mm and with only 83 keys in total, the WK-838 is light with a small footprint which fits perfectly onto a desk with very limited space in a business or home environment.
- **Multimedia Functions** - 9 multimedia keys are on offer at the touch of button creating shortcuts to access some popular media applications.
- **Quality** - The WK-838 made from metal & ABS materials makes the keyboard much stronger and durable ultimately having a longer life span.
- **Full Compatibility** - Compatible with Windows 2000 / XP / ME / 7 / Android / Linux / Mac OS.

## **Specifications**

**Connectivity :** USB

**Keyboard Qty:** 83 Keys

**Cable Length:** 1.3m

**Working Power:** 5V=100mA

**M.T.B.F:** 3 Million Keystrokes

**Multimedia  
Functions:** 9

- 1:** Open Default Web Browser
- 2:** Open Default Media Player Program
- 3:** Play Or Pause Current Media Track
- 4:** Play Previous Media Track
- 5:** Play Next Media Track
- 6:** Increase System Volume
- 7:** Decrease System Volume
- 8:** Stop Current Media Track
- 9:** Mute System Volume

**Key Elasticity:** 55g ± 7g

**Pre-Travel  
Distance of  
Keys:** 1.8mm

**Total Travel  
Distance of  
Keys:** 2.3mm

**Working  
Environment  
Temperature:** 0°C to 45°C

**Operating  
Humidity:** 20%-90%

**Working  
Voltage:** 5V

**Working Current  
:** 100mA (max.)

**Software  
Compatibility:** Windows 2000 / XP / ME / 7 / 8 / 10 / Android / Linux /  
Mac OS

**Net Weight:** 470 ± 20g

## **General Specifications**

**Manufacturer** WK-838

**Part Number:**

**EAN Number:** 5055492407931

**Has Mains Plug:** No

**Colour:** Black

**What's In The** Keyboard

**Box:** User Manual

**Unit (Product)**

**Dimensions** 348mm x 22mm x 145mm (W x H x D)  
**(mm):**

**Packaging**

**Dimensions** 361mm x 160mm x 28mm (W x H x D)  
**(mm):**

**Net Weight** 0.41 KGs  
**(KGs):**

**Gross Weight** 0.6 KGs  
**(KGs):**