

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0190370004**
Status: **Active**
Overview: Snap Plugs and Receptacles
Description: Krimptite Snap Plug Receptacle, for 14-16 AWG Wire, Box, 16.26mm Length

Documents:

[Drawing \(PDF\)](#) [Product Specification PS-19902-013-001 \(PDF\)](#)
[Product Specification PS-19902-011-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
 UL E152602

General

Product Family Quick Disconnects
 Series 19037
 Crimp Quality Equipment Yes
 Insulated No
 Overview Snap Plugs and Receptacles
 Product Name Krimptite
 Type Snap Receptacle
 UPC 800755059014

Physical

Barrel Type Closed
 Gender Female
 Glow-Wire Capable No
 Insulation None
 Lock to Mating Part None
 Material - Metal Brass
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Net Weight 0.617/g
 Orientation Straight
 Packaging Type Bag
 Tab Thickness N/A
 Tab Width N/A
 Wire Insulation Diameter N/A
 Wire Size AWG 14, 16
 Wire Size mm² 1.30-2.00

Electrical


Voltage - Maximum N/A

Material Info

Engineering Number BB-1122

Reference - Drawing Numbers

Product Specification PS-19902-011-001, PS-19902-013-001
 Sales Drawing SD-19037-002



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
 -ED/88/2018 (15
 January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

19037 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool	640031100
Hand Crimp Tool	640031200
Crimp Head for the AT-200 Pneumatic Hand Tool	640071100
Crimp Head for the AT-200 Pneumatic Hand Tool	640071200