

LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN	APVD	
	A	FIRST ISSUE	20MAR06	JMS	FWK	

NOTES

- 1

100 TRAY PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 2

SINGLE PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 3

Au PLATING
- 4

Ni PLATING
5.

CHARACTERISTICS

FREQUENCY RANGE:DC-4GHz

INSULATION RESISTANCE:5000 MOHMS

WORKING VOLTAGE:500V

DIELECTRIC WITHSTAND VOLTAGE:1500V RMS

TEMPERATURE RATE:-55°C TO +85°C


CONTACT RESISTANCE:3 mOHMS
6.

MECHANICAL CHARACTERISTICS

DURABILITY:50 CYCLES
7.

FOR TECHNICAL DATA REFER TO YOUR LOCAL TYCO ELECTRONICS SALES OFFICE
8.

ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED



					1	1	PHOS BRONZE	3	MALE CONTACT	4
					1	1	PHOS BRONZE	3	FEMALE CONTACT	3
					1	1	POLYMETHYLPENTENE		INSULATOR	2
					1	1	ZINC ALLOY	4	BODY	1
					5--1	5--0	MATERIAL		DESCRIPTION	ITEM
QUANTITY PER ASSY							PARTS LIST			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.SANDWELL 20MAR06	tyco Electronics Tyco Electronics Corporation Bideford, UK, EX39 4HE							
DIMENSIONS: mm		CHK S.PARLOW 20MAR06								
		APVD F.WHEELER-KING 20MAR06	NAME BNC ELBOW ADAPTOR PLUG - JACK							
		PRODUCT SPEC	50 OHMS							
		APPLICATION SPEC								
MATERIAL SEE TABLE		WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO C-1634526	RESTRICTED TO -				
CUSTOMER DRAWING							SCALE NTS	SHEET 1	OF 1	REV A