

## Han HD shielded module male



Part number	09 14 027 3013
Specification	Han HD shielded module male
HARTING eCatalogue	<a href="https://b2b.harting.com/09140273013">https://b2b.harting.com/09140273013</a>

### Identification

Category	Modules
Series	Han-Modular®
Type of module	Han® High density shielded module

### Version

Termination method	Crimp termination
Gender	Male
Number of contacts	27
Additional contacts	+ shielding
Details	Please order crimp contacts separately.

### Technical characteristics

Conductor cross-section	0.13 ... 0.33 mm <sup>2</sup>
Rated current	2 A
Rated voltage	16 V
Rated impulse voltage	0.8 kV
Pollution degree	3
Contact resistance, shielding	≤10 mΩ
Limiting temperature	-40 ... +85 °C
Mating cycles	≥500

### Material properties

Material (insert)	LCP
Material (shielding)	Zinc die-cast, nickel-plated
Material flammability class acc. to UL 94	V-0

### Specifications and approvals

Specifications	EN 60664-1
----------------	------------



Pushing Performance

## Specifications and approvals

	IEC 61984
--	-----------

## Commercial data

Packaging size	1
Net weight	34.5 g
Country of origin	Germany
European customs tariff number	85389099