## CTM-652 Small Insulated Alligator Clip

**Datasheet** 

Fully insulated small alligator clip with 4mm safety banana jack...

## **Description**

Fully insulated small safety alligator clip with 4mm safety banana jack. Accepts retractable, sheathed, and standard banana plugs. Jaws open to 0.27" (7 mm).

- Material: Steel, Nickel Plated; Glass-filled Nylon
- Mueller cross: BU-652-\*
- Jaws open to 0.27" (7 mm)
- Length: 3.24" (82 mm)
- Accepts retractable, sheathed, and standard 4mm banana plugs
- Available in 2 colors





All specifications apply to the unit after a temperature stabilization time of 20 minutes over an ambient temperature range of  $25^{\circ}$ C  $\pm$   $5^{\circ}$ C.

## **Specifications**

IEC Rating	1,000 V CAT II / 600 V CAT III
Materials	Steel, Nickel Plt; Nylon
Current Max	20 A
Temperature (degrees)	0 to +60C
RoHS (2011/65/EU)	Compliant

Specifications are subject to change without notice. To ensure the most current version of this manual, please download the current version from our website: caltestelectronics.com

