

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0151670249](#)
Status: **Active**
Overview: Premo-Flex Cable Jumpers
Description: 1.00mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 10 Circuits, 0.076m Cable Length, Tin (Sn) Plating

Documents:

| | |
|--|--|
| Drawing (PDF) | RoHS Certificate of Compliance (PDF) |
| Product Specification PS-15167-001-001 (PDF) | Product Literature (PDF) |
| Packaging Specification PK-15167-001-001 (PDF) | |

General

| | |
|-----------------------------|--|
| Product Family | Cable |
| Series | 15167 |
| Comments | Contacts on the same side, Type A, Contacts on the same side, Type A |
| Crimp Quality Equipment | Yes |
| Overview | <u>Premo-Flex Cable Jumpers</u> |
| Product Literature Order No | 987650-6631 |
| Product Name | Premo-Flex FFC Jumper |
| UPC | 884982851320 |

Physical

| | |
|-------------------------------|-----------------|
| Cable Length | 0.076m |
| Circuits (Loaded) | 10 |
| Circuits (maximum) | 10 |
| Material - Plating Mating | Tin |
| Net Weight | 1.000/g |
| Packaging Type | Bag |
| Pitch - Mating Interface | 1.00mm |
| Temperature Range - Operating | -40° to +105°C |
| Wire Size AWG | N/A |
| Wire/Cable Type | Flat Flex Cable |

Electrical

| | |
|-------------------------------|--------|
| Current - Maximum per Contact | 1.2A |
| Voltage - Maximum | 60V AC |

Material Info

Reference - Drawing Numbers

| | |
|-------------------------|------------------|
| Packaging Specification | PK-15167-001-001 |
| Product Specification | PS-15167-001-001 |
| Sales Drawing | SD-15167-001 |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

15167 Series

Mates With

Easy-On FFC/FPC Connector (be sure to match plating):
 [52207](#) , [52271](#) , [52610](#)