

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0797581016](#)
Status: **Active**
Overview: [Pre-Crimped Leads](#)
Description: Pre-Crimped Lead Pico-Clasp Dual-Row Female-to-Pico-Clasp Dual-Row Female, 150mm, 28 AWG

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	79758
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Pico-Clasp Crimp Terminals
Overview	Pre-Crimped Leads
Product Name	Pico-Clasp
UPC	889056818629

Physical

Cable Length	0.15m
Circuits (Loaded)	1
Color - Resin	Black
Gender	Female-Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.203/g
Packaging Type	Bag
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Size AWG	28
Wire/Cable Type	UL 1571

Material Info

Reference - Drawing Numbers

Sales Drawing	2012341212-000
---------------	----------------



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[79758 Series](#)

Use With

Pico-Clasp Crimp Housing [501189](#)