



60W

VT-8-62 60W LED BATTEN FITTING-152CM WITH SAMSUNG CHIP
COLROCODE:4000K -5 YRS WARRANTY

Lumens
6900

Beam Angle
120

Dimensions
1524x64x62mm

Day White
SKU:756

5 YEARS
WARRANTY



Technical Information

Watts: **60**

Lumens: **6900**

Beam Angle: **120**

Body Type: **PC + Iron**

Long life: **30,000 Hours**

LED Chip Type: **SMD-Samsung Chip**

IP Rating: **IP20**

Dimmable: **No**

Warranty (Years): **5**

PF: **>0.9**

CRI: **>80**

Operation Temperature: **-20°C to +45°C**

Input Power: **AC:220-240V/50Hz**

Sensor Compatibility: **Yes**

Features

- ✓ V-TAC's Batten fittings designed with Tp(A) rated diffuser to meet the fire safety standards
- ✓ LED Batten fittings designed with LED chip by Samsung deliver high performance light output of 120 lumens/watt.
- ✓ Programmable Driver with DIP switch.
- ✓ Built strong using the materials Iron + Polycarbonate
- ✓ Flicker Free
- ✓ Complies with LM-80
- ✓ Optional emergency pack and microwave sensor specially designed for LED Batten are also available
- ✓ Applications - Ideal for Commercial and Residential applications.



Note: Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	1.93
Unit CBM	0.009056

Listing Details

EAN Code	3800157638197
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	10
---------------------------------	----

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES