

9W

VT-810 9W LED WALL LAMP COLORCODE:4000K BLACK



Lumens
720

Beam Angle
100

Dimensions
400x100x94mm

Day White
SKU:8269

3 YEARS
WARRANTY

SENSOR
COMPATIBLE



Technical Information

Instant Start: 0-100% in 1s

Watts: 9

Lumens: 720

Beam Angle: 100

Unit Color: Black

Body Type: Plastic + Metal

Long life: 30,000 Hours

LED Chip Type: SMD

IP Rating: IP20

Dimmable: No

Warranty (Years): 3

PF: >0.5

CRI: >80

Operation Temperature: -20 to +45°C

Input Power: AC 220-240V, 50/60Hz

Sensor Compatibility: Yes

Features

- ✓ Perfect choice of Interior lighting for fabulous aesthetics and appeal
- ✓ High quality LED chips for a reliable lighting effect
- ✓ Efficient LED Driver & intruded heat sink for reliable lifespan
- ✓ Portability and ease of maintenance
- ✓ Available in different color options - Warm White and Day White
- ✓ Applications - Residential, Building, Restaurants, Décor etc

Note:



Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	0.612
Length(Box)mm	110
Width(Box)mm	400
Height(Box)mm	100
Unit CBM	0.0044

Listing Details

EAN Code	3800157627191
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	12
Qty Per Pallet	240

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES