



Hybrid-Compressor

PRESSITO

Item No.: 4020460

Ident No.: 11017

Bar Code: 4006825627244

The Einhell hybrid compressor Pressito can be operated using either a power cable or an 18 Volt system battery from the Power X-Change series. The compressor has a high-pressure pump for car / cycle tires and balls and a low-pressure pump / low-pressure suction function for air mattresses and rubber dinghies (6in1-function). A 3-piece inflation adapter set is included. The compact and light compressor can be stowed away easily and, thanks to the rechargeable battery, can also be taken along.

Features & Benefits

- A member of the Power X-Change family
- Hybrid function: for use with a power cable/rechargeable battery
- High-pressure pump for inflating car tires, cycle tires, balls
- Low-pressure pump for inflating air mattresses
- Low-pressure suction facility for deflating air mattresses
- Easy-to-operate manual digital pressure indicator
- High-pressure pump with adjustable pressure settings up to 11 bar
- With auto shutoff function when adjusted pressure is reached
- Integrated storage holder for the 3-piece inflation adapter set
- Supplied without battery and charger (available separately)

Technical Data

- Engine power	90 W
 Suction capacity high pressure pump 	21 L/min
- Output power at 0 bar	16 L/min
- Output power at 4 bar	10 L/min
- Output power at 7 bar	8 L/min
- Max. operating pressure high pressure pump	11 bar
- Hose length	710 mm

Logistic Data

- Product weight (kg)	2.1052
- Gross weight (kg)	2.6286
- Dimensions single packaging	300 x 190 x 222 mm
- Pieces per export carton	4 Pieces
- Gross weight of export carton	10.41 kg
- Dimensions export carton	390 x 310 x 460 mm
- Container quantity (20"/40"/40"HC)	2120 4360 4960







