





Multifunctional Tool

TC-MG 220/1 E

Item No.: 4465095

Ident No.: 11017

Bar Code: 4006825626490

The Einhell multifunctional tool TC-MG 220/1 E enables sanding, scraping or sawing jobs to be performed with just a single tool. Accessories are changed with ease thanks to the magnetic tool fixation with universal screw. The multifunctional tool is equipped with a four-pin tool chuck. The powerful 220 W motor as well as the speed electronics enable material and application suitable working. Safe and pleasant working enables the soft grip. The scope of delivery includes a delta grinding/sanding plate, six sheet of abrasive paper (3*P60/3*P120), one scraper, one plunge-cut saw blade for wood and plastic, a dust extraction adapter and a hexagon key.

Features & Benefits

- Comfortable accessory change thanks to magnetic tool fixation
- Powerful 220 Watt motor
- Speed electronics for material and application suitable working
- Safe and pleasant working thanks to soft grip
- 4-pin-tool fixation for flexible positioning of equipment
- Incl. triangular grinding/sanding plate
- Incl. 6x grinding/sanding paper (3*P60/3*P120)
- Incl. scraper
- Incl. plunge-cut saw blade for wood and plastic
- Incl. convenient dust extraction adapter
- Incl. hexagon key



Technical Data


- Mains supply 220-240 V | 50 Hz

- Power 220 W

- Oscillating speed

- Angle of oscillation

- Sandpaper size



Logistic Data

- Product weight 1.26 kg - Gross weight single packaging 1.65 kg

- Dimensions single packaging 330 x 110 x 90 mm

- Pieces per export carton 9 Pieces - Gross weight export carton 15 ka

- Dimensions export carton 360 x 350 x 295 mm - Container quantity (20"/40"/40"HC) 6534 | 11493 | 0















Available as special accessories



Fliesen-Set Multifunctional Tool Accessory Item No.: 4465017 Bar Code: 4006825625523 Einhell Accessory



Boden- und Einbau-Set Multifunctional Tool Accessory Item No.: 4465016 Bar Code: 4006825625516 Einhell Accessory