



## Main

Range of product	Harmony XVR
Product or component type	Prewired rotating mirror beacon
Sound signalling	Buzzer
Device short name	XVR
Mounting diameter	120 mm
IP degree of protection	IP23 conforming to IEC 60529
[Us] rated supply voltage	12 V AC/DC
Light source	High luminosity LED, blue
Noise level	50...90 dB (continuous or intermittent tone) at 1 m

## Complementary



Material	ABS (acrylonitrile butadiene-styrene) (body part) AS (globe)
CAD overall width	120 mm
CAD overall depth	120 mm
Product weight	0.5 kg
Marking	CE
Product mounting	By 3 M5 screws
Supply voltage limits	10...15 V DC 10.8...13.2 V AC
[Uimp] rated impulse withstand voltage	0.8 kV
Current consumption	333 mA
Flashing frequency	2.3 Hz
Clamping connection capacity	0.83 mm <sup>2</sup>
AWG gauge	AWG 18
Cable length	400 mm

## Environment

Standards	EN 61000-6-2
-----------	--------------

Protective treatment	TC
Ambient air temperature for storage	-35...70 °C
Ambient air temperature for operation	-10...50 °C
Electrical shock protection class	Class II conforming to IEC 61140

### Offer Sustainability


Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1611 - Schneider Electric declaration of conformity <a href="#"> Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#"> End of Life Information</a>
Product end of life instructions	Available

### Contractual warranty

Warranty period	18 months
-----------------	-----------

## Rotating Mirror Beacon

## Dimensions



Rotating Mirror Beacon

Panel Cut-out

