



Electronics Cleaners - Liquid Comparison Chart

<i>Cat. Number</i>	824	8241	4050	434
<i>Cleaning Characteristics</i>				
PLASTIC SAFE	Yes	Yes	Yes	No
FLAMMABLE	Yes	Yes	Yes	Yes
STRENGTH	Regular	Regular	Regular	Extra
EVAPORATION	Moderate	Moderate	Moderate	Fast
<i>Regulatory Status</i>				
NSF COMPLIANT	Yes	No	No	No
VOC FREE	No	No	No	Yes
<i>Physical Properties</i>				
FLASH POINT	12 °C / 54°F	-18 °C / 65 °F	13 °C / 55 °F	-17 °C / 1.4 °F
BOILING POINT	81.8 °C / 179 °F	81 °C / 177 °F	78 °C / 174 °F	56 °C / 133 °F
<i>Contaminants Cleaning Efficiency</i>				
NON-POLAR RESIDUES	Good	Fair	Good	Good
POLAR RESIDUES	Fair	Good	Fair	Fair
IONIC RESIDUES <small>water soluble</small>	Fair	Good	Fair	Good
FLUX RESIDUES	Good	Fair	Good	Good
OILS	Good	Fair	Good	Good
GREASES	Fair	Fair	Good	Good
INKS	Fair	Fair	Good	Good
DIRT & GRIMES	Fair	Fair	Fair	Fair