

## ONE-WRAP #29 (EUROPEAN)

### **Construction characteristics**

Base material Construction	Polypropylene & Velour PA Extruded and Laminated
Width	Nominal $\pm 1\%$
Overall thickness	$1.35 \pm 0.20$ mm
Weight	$550 \pm 60$ g/m <sup>2</sup>
Hooks/cm <sup>2</sup> (type #29)	$266 \pm 10\%$
Colours	White, black, yellow, green, blue and red
Hook colours	Natural except for black and white, where hook is black and white.

### **Usage characteristics**

Peel strength*	Minimum 0.4 N/cm
Shear strength*	Minimum 7.0 N/cm <sup>2</sup>
Cycle life*	50% loss 100 cycles
Breaking strength*	Minimum 120 N/cm
Melting point	150°C
Electric conductivity	None
Washing resistance	Good
UV resistance	Low
Humidity resistance	Medium
Sewn resistance	Low
Acid resistance	Medium

\* Internal Norm of VESA

The information in this Technical Sheet is based on reliable tests and trials. Given the diversity of the use of our products we advise our customers to ensure themselves that the product meets the requirements of their application. The responsibility for the application and use of the product remains with the customer.