




## Han M23 ComLock-S Hood 3-7 mm



Part number	09 15 100 0481
Specification	Han M23 ComLock-S Hood 3-7 mm
HARTING eCatalogue	<a href="https://b2b.harting.com/09151000481">https://b2b.harting.com/09151000481</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> M23 Signal
Type of hood/housing	Hoods
Description of hood/housing	EMC version

### Version

Locking type	ComLock-S rapid locking
Size	M23
Version	Top entry
Details	Compatible to Speedtec (TE)

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP67 in locked position IP69 / IPX9K acc. to ISO 20653 in locked position
Clamping range	3 ... 7 mm

### Material properties

Material (hood/housing)	Copper-zinc alloy
Surface (hood/housing)	Nickel plated

### Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
----------	-----------------------



Pushing Performance

## Commercial data

Packaging size	5
Net weight	90.8 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors