




Pushing Performance

Han M23 ComLock-S Hood 7-12 mm



Part number	09 15 100 0482
Specification	Han M23 ComLock-S Hood 7-12 mm
HARTING eCatalogue	https://b2b.harting.com/09151000482

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] M23 Signal
Type of hood/housing	Hoods
Description of hood/housing	EMC version

Version

Locking type	ComLock-S rapid locking
Size	M23
Version	Top entry
Details	Compatible to Speedtec (TE)

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP67 in locked position IP69 / IPX9K acc. to ISO 20653 in locked position
Clamping range	7 ... 12 mm

Material properties

Material (hood/housing)	Copper-zinc alloy
Surface (hood/housing)	Nickel plated

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
----------	-----------------------

Commercial data

Packaging size	5
Net weight	89.4 g
Country of origin	Germany



Pushing Performance

Commercial data

European customs tariff number 85366990
