

Han M23 male-c 1mm (0,08 – 0,56mm²) Au



Part number	09 15 100 6101
Specification	Han M23 male-c 1mm (0,08 – 0,56mm ²) Au
HARTING eCatalogue	https://b2b.harting.com/09151006101

Identification

Category	Contacts
Series	Han [®] M23 Signal
Type of contact	Crimp contact
Description of the contact	Turned 1 mm

Version

Gender	Male
--------	------

Technical characteristics

Conductor cross-section	0.08 ... 0.56 mm ²
Conductor cross-section	AWG 28 ... AWG 20
Contact resistance	≤3 mΩ
Stripping length	4 mm

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Specifications	EN 60664-1
----------------	------------



Pushing Performance

Specifications and approvals

IEC 61984

Commercial data

Packaging size	100
Net weight	0.25 g
Country of origin	France
European customs tariff number	85366990