

## Han M23 female-c 1mm (0,75 – 1,50mm<sup>2</sup>) Au



Part number	09 15 100 6203
Specification	Han M23 female-c 1mm (0,75 – 1,50mm <sup>2</sup> ) Au
HARTING eCatalogue	<a href="https://b2b.harting.com/09151006203">https://b2b.harting.com/09151006203</a>

### Identification

Category	Contacts
Series	Han <sup>®</sup> M23 Signal
Type of contact	Crimp contact
Description of the contact	Turned 1 mm

### Version

Gender	Female
--------	--------

### Technical characteristics

Conductor cross-section	0.75 ... 1.5 mm <sup>2</sup>
Conductor cross-section	AWG 19 ... AWG 16
Contact resistance	≤3 mΩ
Stripping length	4 mm

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

### Specifications and approvals

Specifications	EN 60664-1
----------------	------------



Pushing Performance

## Specifications and approvals

	IEC 61984
--	-----------

## Commercial data

Packaging size	100
Net weight	0.6 g
Country of origin	Germany
European customs tariff number	85366990