




Pushing Performance

## M12-PCB-SMT-2PC-4P-ACOD-F-STR(75)



Part number	21 03 311 2411
Specification	M12-PCB-SMT-2PC-4P-ACOD-F-STR(75)
HARTING eCatalogue	<a href="https://b2b.harting.com/21033112411">https://b2b.harting.com/21033112411</a>

### Identification

Category	Connector
Series	Circular connectors M12
Element	PCB adapter
Specification	Straight

### Version

Termination method	Reflow soldering termination (SMT)
Gender	Female
Shielding	Unshielded
Number of contacts	4
Coding	A-coding
Pack contents	Tape & reel

### Technical characteristics

Rated current	4 A
Rated voltage	250 V
Rated impulse voltage	1.5 kV
Pollution degree	3
Insulation resistance	$> 10^8 \Omega$
Contact resistance	$\leq 10 \text{ m}\Omega$
Ambient temperature	-40 ... +85 °C
Mating cycles	$\geq 100$
Overvoltage category	III



Pushing Performance

## Technical characteristics

Isolation group I ( $600 \leq CTI$ )

## Material properties

Material (insert)	LCP
Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

## Specifications and approvals

Specifications	IEC 61076-2-101
----------------	-----------------

## Commercial data

Packaging size	1
Net weight	689 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440402 PCB connector