

SPECIFICATIONS

Power requirement	5V DC @ 2A
Output DDC signal	5 Volts p-p (TTL)
Max baud rate	10.2Gbps
Max bandwidth	340MHz
Deep Colour	36 bit
Max Single Link Range	3840x2160
Dimensions	270 x 130 x 20mm
Weight (not inc PSU)	1.08kg
Operating Temperature	0°C to +70°C
Operating Humidity	10% to 85% RH (no condensation)