


Category 6A 24 Port Patch Panel



Category 6A 24 Port Patch Panel (SGFK24)

TUK's high density horizontal Category 6A FTP patch panel offers high performance at a competitive price. Based on our component level keystone (SGKSje), this panel can be terminated quickly and easily with a variety of cables.

Features

- High performance compliant with ANSI/TIA 568 C.2 standard at component level
- Compliant with IEC60512-99-001 suitable for use with IEEE 802.3at (PoE+) applications
- 3rd Party (Delta) verified
- Suitable for 23-26 AWG stranded and solid wire. (0.40 0.57mm)
- Fully shielded die-cast keystone body is robust as well as offering outstanding performance in eliminating alien cross-talk
- Quick and easy tool-less "butterfly" style termination
- · Built-in retracting dustcovers
- Clear numbering on the front provides a quick, easy way to identify cable run
- 'Write on' label facility for port identification
- Supplied with a fixed rear cable management bar, cable ties, 4 sets of M6 black cage nuts and 25cm long earth wire with fixing screws



Specifications

Weight: 1.3kg approx.

• Dimensions: 483 x 102.5 x 44.5 (W x D x H) approx.

Colour:

front: black + silver

rear: silver

Material:

Panel: cold-rolled steel sheet 1.5mm thick

Rear of panel and cable management: nickel plated

Contacts: 50µ"/1.27µm gold plating over nickel over phosphor bronze

Keystone housing: Zinc alloy

Packaging: Supplied as a kit in an individual carton

EAN: 5055386507440

Commodity Code: 85177090

For further information, please see links below:

SGKSje: http://www.tuk.co.uk/tuk_live/product_details.php?category_id=&pld=398
FFK24mtpt: http://www.tuk.co.uk/tuk_live/product_details.php?category_id=&pld=398

