



# TRIAx

connecting the future



## LTE WFAV 25 - 1 Input - Wideband Masthead Amplifier & Power Supply Kit

Article number: 370559

### Product description:

#### Wolsey LTE Masthead Amplifier Kit

- F-Connector Masthead Amplifier and Power Supply Kit
- 1 Input 1 Output
- 10-25 dB Variable Gain
- Weatherproof housing
- Fully screened enclosure

### Specifications

ORDER INFORMATION	
EAN Number	5702663705593
CHARACTERISTICS	
Type	Amplifier - mast
Max. Output level (@ -60dB IMD)	102 dBμV
FREQUENCY	
Input 1 - frequency	470...790 MHz
Input 1 - band	UHF (T)

Input 1 - channels	21...60
LTE protection	@ 800Mhz
<b>GAIN</b>	
Input 1 - gain	10-25 dB
Input 1 - noise figure	<2.2 dB
<b>RETURN LOSS</b>	
Return Loss	10 Typ dB
<b>ELECTRICAL</b>	
Impedance	75 $\Omega$
<b>OPERATIONAL</b>	
DC Operating voltage	12 VDC
DC Current consumption	100 mA
<b>CONNECTORS</b>	
Number of inputs	1
Number of outputs	1
Connector Type	F-female
<b>MECHANICAL</b>	
Product Height	215 mm
Product Depth	60 mm
Product Width	120 mm
Colour	Black
Packaging Depth	5,000 m
Net Weight	0,560 kg
Tara Weight	0,060 kg
Total Weight	0,620 kg
Remarks	Kit includes WPS 100 Power Supply, 12VDC, 100mA Max Fully screened