

WSM 1C SOLDSTWBATTERY 100-230V UK F/G



² and soldering tip RT 3, chisel 1,3 mm and

Benefits

- › Solution for service technician
- › 50 W
- › Recharged in 20 minutes.

For this purpose, we recommend:



Solder fume extractors



Soldering irons



Cleaning



Pre-heating plates



Technical Data

Dimensions L x W x H (mm)	137 x 110 x 55
Dimensions L x W x H (inches)	5,39 x 4,33 x 2,17 Inch
Weight (approx.) in kg	0.41
Voltage	100-240 V AC / 12 V DC
Power	50 W
Channels	1
Temperature range (depends on tool) °C	100 - 400
Temperature range (depends on tool) °F	210 - 750
Temperature accuracy °C	± 9
Temperature accuracy °F	± 17
Temperature stability °C	± 5
Temperature stability °F	± 9
Equipotential bonding socket	Via 3,5 mm pawl socket on side of device
Display	Touch-Sensor-Technology
Air consumption l/min	---
Operating pressure in bar/psi	---
Capacity l/min	---
Vacuum	---

Owning the bench



PROFESSIONAL



FILTRATION



EREM



XCELITE